PRODUCT INFORMATION

DURATECH

MOP 250x50-Ø40 HL60

EAN 4031582320077



Image may differ from the original product

WHEEL

Body material	Polyamide, super heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	9.84 in
Tread width	1.97 in
Axle hole diameter	1.57 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (D)	75 Shore D
Bearing type	6308

PERFORMANCE

Roll Performance	●●●●●
Movement noise	●●○○○
Attrition	●●●●●
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	9259.4 lb
Load capacity at 3.7 mph	7716.17 lb
Electric conductive	no
Stainless	no
Load capacity Static	18518.81 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	8.58 lb

© Copyright 2026 TENTE International GmbH


DURATECH

MOP 250x50-Ø40 HL60

EAN 4031582320077

Order number 00801034

Product Drawings




© Copyright 2026 TENTE International GmbH

DURATECH

MOP 250x50-Ø40 HL60

EAN 4031582320077

Order number 00801684



© Copyright 2026 TENTE International GmbH