

# DURATECH PLUS

MMP050x26-Ø15

EAN 4031582399370



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                            |
|-----------------------|----------------------------|
| Body material         | Polyamide, super heavy     |
| Tread material        | Double flanged with tracks |
| Bearing               | Precision ball bearing     |
| Threadguards          | Without threadguard        |
| Diameter              | 1.97 in                    |
| Tread width           | 1.02 in                    |
| Axle hole diameter    | 0.59 in                    |
| Hub length            | 1.26 in                    |
| Hardness of tread (D) | 75 Shore D                 |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                              |
|-----------------------------|------------------------------|
| Product name                | Duratech plus                |
| Type                        | Wheel                        |
| Standard                    | EN12533 - Heavy Duty Castors |
| Load capacity at 2.5 mph    | 529.11 lb                    |
| Load capacity at 3.7 mph    | 440.92 lb                    |
| Electric conductive         | no                           |
| Stainless                   | no                           |
| Load capacity Static        | 1058.22 lb                   |
| Temperature range (Minimum) | -40 °F                       |
| Temperature range (Maximum) | 176 °F                       |

# DURATECH PLUS

MMP050x26-Ø15

EAN 4031582399370

Order number 00860912  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

