

# LINEA LIGHT

5925PJI075S70-10x15/10 scan RAL9002

EAN 4031582420548



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                                |
|-----------------------------|--------------------------------|
| Product name                | Linea light                    |
| Type                        | Swivel caster with wheel brake |
| Standard                    | EN12528 - Furniture Castors    |
| Load capacity at 1.8 mph    | 66.14 lb                       |
| Electric conductive         | no                             |
| Stainless                   | no                             |
| Load capacity Static        | 132.28 lb                      |
| Temperature range (Minimum) | -4 °F                          |
| Temperature range (Maximum) | 140 °F                         |
| Overall height              | 3.13 in                        |
| Overall width               | 2.17 in                        |
| Overall weight              | 0.41 lb                        |

## HOUSING

|                     |                      |
|---------------------|----------------------|
| Housing Material    | Polyamide            |
| Fork shape          | Twin wheel housing   |
| Swivel bearing      | Stem, swiveling      |
| Housing Color       | Gray white (RAL9002) |
| Offset              | 0.91 in              |
| Swivel radius       | 3.23 in              |
| Swivel interference | 6.46 in              |
| Thread diameter     | 0 in                 |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polypropylene                  |
| Tread material        | Thermoplastic rubber           |
| Bearing               | Plain bearing with spacer tube |
| Threadguards          | Without threadguard            |
| Diameter              | 2.95 in                        |
| Tread width           | 0.59 in                        |
| Hardness of tread (A) | 92 Shore A                     |

## FITTING

|               |                                      |
|---------------|--------------------------------------|
| Fitting type  | Threaded stem with hexagon neck, top |
| Stem diameter | 0.39 in                              |
| Stem length   | 0.59 in                              |



Deutscher  
Designer  
Club



Interzum  
Award



product  
design  
award

IF Design  
Award

# LINEA LIGHT


5925PJI075S70-10x15/10 scan RAL9002

EAN 4031582420548



BETTER MOBILITY. BETTER LIFE.

## Product Drawings



Deutscher  
Designer  
Club



Interzum  
Award



product  
design  
award

IF Design  
Award