

ZETA

4681ITP125P63 soft cv

EAN 4031582337624



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ● ○
Corrosion Resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Zeta
Type	Swivel castor with directional lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	400 kg
Load capacity at 6 km/h	320 kg
Electric Conductive	No
Stainless	No
Load capacity Static	800 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall Height	164 mm
Overall width	96 mm
Overall weight	2.91 kg

HOUSING

Housing Material	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel Bearing	Two ball races, reinforced or stainless
Housing Color	Blue passivated
Offset	55 mm
Swivel radius	117.5 mm
Swivel interference	235 mm
Dome diameter	96 mm

WHEEL

Tread profile	convex
Tread hardness	soft
Body material	Aluminium
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel Color	Traffic grey A (RAL7042)
Threadguards	Without threadguard
Diameter	125 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	80 Shore A

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

ZETA

4681ITP125P63 soft cv

EAN 4031582337624

Order number 00838059

Product Drawings



BETTER MOBILITY. BETTER LIFE.

