

# MONO

A020PJI050L51-10 chrome

EAN 4031582364583



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product Name	Mono
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	30 kg
Electric Conductive	No
Stainless	No
Load capacity Static	60 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	72 mm
Overall weight	0.54 kg

## HOUSING

Housing Material	Polypropylene
Fork shape	Closed
Swivel Bearing	Stem, swiveling
Housing Color	Chrome
Offset	25 mm
Swivel radius	52.2 mm
Swivel interference	104.4 mm

## WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	50 mm
Tread width	18 mm
Hardness of tread (A)	85 Shore A

## FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

# MONO

A020PJI050L51-10 chrome

EAN 4031582364583



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

