

# AGILA CARE US

2447UAP150R05-28

EAN 4031582300574



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Agila care US                 |
| Housing type                | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 3 km/h     | 150 kg                        |
| Load capacity Static        | 300 kg                        |
| Temperature range (Minimum) | -40 °C                        |
| Temperature range (Maximum) | 80 °C                         |
| Overall height              | 193 mm                        |
| Overall weight              | 1.531 kg                      |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polyamide              |
| Tread material        | Polyurethane, injected |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 150 mm                 |
| Tread width           | 32 mm                  |
| Hardness of tread (D) | 40 Shore D             |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Material fork       | Steel sheet, medium    |
| Fork shape          | Broad                  |
| Swivel bearing      | Precision ball bearing |
| Offset              | 50 mm                  |
| Swivel interference | 250 mm                 |

## FITTING

|               |                   |
|---------------|-------------------|
| Fitting type  | Solid stem, round |
| Bolt diameter | 28 mm             |
| Bolt length   | 45 mm             |