

ALPHA STAINLESS

8470UOD080P30-11

EAN 4031582377149



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	150 kg
Load capacity Static	300 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall height	108 mm
Overall weight	0.663 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Roller bearing, stainless
Axle	Screwed with nut
Diameter	80 mm
Tread width	34 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	44.5 mm
Swivel radius	84.5 mm
Swivel interference	169 mm
Stainless	✓

FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm

ALPHA STAINLESS

8470UOD080P30-11

EAN 4031582377149



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

8470UOD080P30- $\phi 11$

