

PRODUCT INFORMATION

NOVATECH

ETY080x20-Ø20 HL14

EAN 4031582419047



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Load capacity at 1.8 mph	308.65 lb
Electric conductive	no
Stainless	no
Load capacity Static	617.29 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.66 lb

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing (RS/2RS)
Diameter	3.15 in
Tread width	0.79 in
Axle hole diameter	0.79 in
Hub length	0.55 in
Hardness of tread (A)	92 Shore A

