

PRODUCT INFORMATION

ELASTECH

RK.XLR 125x40-Ø20 HL44 ESD

EAN 4031582508383



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	352.74 lb
Electric conductive	no
Stainless	no
Load capacity Static	705.48 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	0.85 lb

WHEEL

Tread hardness	soft
Body material	Undefined
Tread material	Polypropylene, soft
Diameter	4.92 in
Tread width	1.57 in
Hardness of tread (A)	63 Shore A

WB. XLR125x40-Ø20NL44 antistatic

