PRODUCT INFORMATION

ELASTECH

RK.XLR 125x40-Ø20 HL44 ESD

EAN 4031582508383

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Undefined
Tread material	Polypropylene, soft
Diameter	4.92 in
Tread width	1.57 in
Hardness of tread (A)	63 Shore A

PERFORMANCE

Roll Performance	●●●●○
Movement noise	●●●●○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	352.74 lb
Electric conductive	no
Stainless	no
Load capacity Static	705.48 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	0.85 lb

© Copyright 2026 TENTE International GmbH


ELASTECH

RK.XLR 125x40-Ø20 HL44 ESD

EAN 4031582508383

Order number 10011100

Product Drawings



© Copyright 2026 TENTE International GmbH