

PURETECH AIR

DQR400X100-Ø25 HL74 4PR

EAN 4031582318203



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Čelik lista
materijal omotaca	Pneumatička guma, profil bloka
Nošenje	kotrljajući lezaj
štitnici omotaca	Bez stražara
Prečnik	400 mm
Širina omotac	100 mm
dimenzija rupa osovine	25 mm
dužina glavčine	74 mm
Teškoća gazećeg omotac (A)	55 Šor A

PERFORMANSE

Performanse kotrljanja	● ○ ○ ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech air
Tip kućišta	Tocak
Nosivost na 3 km/h	200 kg
Statički Nosivost	400 kg
Ukupna težina	2,44 kg

PURETECH AIR

DQR400X100-Ø25 HL74 4PR

EAN 4031582318203



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

