

# PURETECH

DVR080x30-Ø12 TRG

EAN 4031582403039



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ○ ○ ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Puretech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 70 kg                         |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 140 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall weight              | 0.23 kg                       |

## WHEEL

|                       |                     |
|-----------------------|---------------------|
| Body material         | Sheet Steel         |
| Tread Material Mix    | Solid rubber, black |
| Bearing               | Roller bearing      |
| Threadguards          | Without threadguard |
| Diameter              | 80 mm               |
| Tread width           | 30 mm               |
| Axle Hole Diameter    | 12 mm               |
| Hub Length            | 44.4 mm             |
| Hardness of tread (A) | 85 Shore A          |

# PURETECH

DVR080x30-Ø12 TRG

EAN 4031582403039



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

