

# AGILA

2477PIP100P30-11

EAN 4031582362039



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Agila
Tip	Okreni Tocak sa potpuna kocnica
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	80 kg
Statički Nosivost	160 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	135 mm
Ukupna težina	0,76 kg

## TOCAK

Materijal za telo	polipropilen
	mekan
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	100 mm
Širina omotac	32 mm
Teškoća gazećeg omotac (A)	75 Šor A

## KUCISTE

Materijal	Čelični list, srednji
oblik viljuska	siroko
okretni lezaj	Dve lopte
ofset	43,5 mm
okretni radijus	131 mm
Otpor okretanju	262 mm

## PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	11 mm
Savet	Kastori se mogu montirati standardnim vijcima bilo koje dužine.

# AGILA

2477PIP100P30-11

EAN 4031582362039



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

