

PRODUCT INFORMATION

PURETECH AIR

DQP400x100-Ø10 HL74 4PLY with axle

EAN 4031582438215



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Puretech air
Type	Wheel
Load capacity at 3 km/h	200 kg
Electric Conductive	No
Stainless	No
Load capacity Static	400 kg
Overall weight	2.67 kg

WHEEL

Tread hardness	soft
Body material	Sheet Steel
Tread Material Mix	Pneumatic tyre, block profile
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	400 mm
Tread width	100 mm
Axle Hole Diameter	10 mm
Hub Length	74 mm
Hardness of tread (A)	55 Shore A

PURETECH AIR

DQP400x100-Ø10 HL74 4PLY with axle

EAN 4031582438215



BETTER MOBILITY. BETTER LIFE.

Product Drawings

