

LINEA LIGHT

A920YGI075L51-10 RAL 7001

EAN 4031582399042



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ● ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Linea light
Tip	Okretanje Tocak
Standard	EN12528 - tockovi za nameštaj
Nosivost na 3 km/h	60 kg
Električni provod	yes
nerdjajuci	no
Statički Nosivost	120 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	40 °C
Sveukupna visina	75.5 mm
Ukupna širina	55 mm
Ukupna težina	0.15 kg

KUCISTE

Materijal kućišta	polipropilen
oblik viljuska	kuciste za dva Tocak
okretni lezaj	stablo , okretanje
Boja	Srebrna siva (RAL7001)
okretni radijus	65 mm
Otpor okretanju	130 mm
Prečnik kupole	30 mm

TOCAK

Materijal za telo	polipropilen, električni provodnik
materijal omotaca	Termoplastična guma, električna provodljivost
Nošenje	klizni lezaj sa caura cevi
stitnici omotaca	Bez stražara
Prečnik	75 mm
Širina omotac	15 mm
Teškoća gazećeg omotac (A)	87 Šora A

PRILAGOĐAVANJE

Tip uklapanja	zatvorena rupa za postavljanje B10
dimenzija rupa sraf	10 mm

Deutscher
dizajner
ClubInterzum
nagradaproduct
design
awardIF
nagrada
za Dizajn

LINEA LIGHT


A920YGI075L51-10 RAL 7001

EAN 4031582399042



BETTER MOBILITY. BETTER LIFE.

Crteži proizvoda



Deutscher
dizajner
Club



Interzum
nagrada



product
design
award

IF
nagrada
za Dizajn