PRODUCT INFORMATION

LUMINA

AA25PJI050S70-10X15 TFR

EAN 4031582385649



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Lumina
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	59 mm
Overall width	55 mm
Overall weight	0.1 kg

HOUSING

Housing Material	Polypropylene
Fork shape	Twin wheel housing, closed
Swivel Bearing	Stem, swiveling
Swivel radius	63 mm
Swivel interference	126 mm
Thread diameter	10 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	50 mm
Tread width	10 mm
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	10 mm
Stem length	15 mm

© Copyright 2026 TENTE International GmbH