

ELASTECH

IFP125X50-Ø25

EAN 4031582319804
Broj porudžbine 00830807

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Aluminijum
materijal omotaca	Elastična guma, neobeležena, vulkanizovana
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	50 mm
dimenzija rupa osovina	25 mm
dužina glavcine	60 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	300 kg
Nosivost na 6 km/h	240 kg
Statički Nosivost	600 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	0,844 kg

ELASTECH

IFP125X50-Ø25

EAN 4031582319804
Broj porudžbine 00830807



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

