

# ZETA REVERSE

468SUOP200P63

EAN 4031582398458  
Order number 00860854



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                                   |
|-----------------------------|---------------------------------------------------|
| Product name                | Zeta reverse                                      |
| Housing type                | Swivel castor with spring loaded directional lock |
| Standard                    | EN12532 - Transport Equipment                     |
| Load capacity at 2.5 mph    | 1763.7 lb                                         |
| Load capacity at 3.7 mph    | 1410.96 lb                                        |
| Load capacity Static        | 3527.39 lb                                        |
| Temperature range (Minimum) | -22 °F                                            |
| Temperature range (Maximum) | 176 °F                                            |
| Overall height              | 9.45 in                                           |
| Overall width               | 3.78 in                                           |
| Overall weight              | 7.03 lb                                           |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polyamide                 |
| Tread material        | Identical with wheel body |
| Bearing               | Precision ball bearing    |
| Axle                  | Screwed with nut          |
| Wheel color           | Natural white             |
| Threadguards          | With threadguard          |
| Diameter              | 7.87 in                   |
| Tread width           | 1.97 in                   |
| Body width            | 1.97 in                   |
| Hardness of tread (D) | 75 Shore D                |

## HOUSING

|                     |                                         |
|---------------------|-----------------------------------------|
| Material            | Steel sheet, very heavy                 |
| Fork shape          | Broad, reinforced                       |
| Swivel bearing      | Two ball races, reinforced or stainless |
| Color               | Blue passivated                         |
| Offset              | 2.17 in                                 |
| Swivel radius       | 6.1 in                                  |
| Swivel interference | 12.2 in                                 |
| Dome diameter       | 3.78 in                                 |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 5.39 in           |
| Plate width                 | 4.13 in           |
| Plate hole length (Minimum) | 2.95 in           |
| Plate hole length (Maximum) | 3.15 in           |
| Plate hole width (Minimum)  | 2.95 in           |
| Plate hole width (Maximum)  | 4.13 in           |
| Plate hole diameter         | 0.43 in           |

# ZETA REVERSE

468SUOP200P63

EAN 4031582398458  
Order number 00860854



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

