

SUPRATECH

PJO3.5X1.25-Ø0.5 HL40

EAN 4031582436051



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	3.5 in
Tread width	1.25 in
Axle hole diameter	0.48 in
Hub length	1.57 in
Hardness of tread (A)	77 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Housing type	Wheel
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 1.8 mph	209.44 lb
Load capacity Static	418.88 lb

SUPRATECH

PJO3.5X1.25-Ø0.5 HL40

EAN 4031582436051



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

