

# NOVATECH

ETX085X95-Ø25 HL100-F

EAN 4031582453034



Image may differ from the original product

## WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing, sealed
Threadguards	With threadguard
Diameter	85 mm
Tread width	95 mm
Axle hole diameter	25 mm
Hub length	100 mm
Hardness of tread (A)	92 Shore A
Bearing type	6006 2RS
Sealing type	A
Suitable for	linde_mic

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Load capacity at 3 km/h	1000 kg
Load capacity Static	2000 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	1.416 kg

# NOVATECH

ETX085X95-Ø25 HL100-F

EAN 4031582453034



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

