

NOVATECH

FTP 250x100-Ø35 HL120

EAN 4031582319361



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL


Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	9.84 in
Tread width	3.94 in
Axle hole diameter	1.38 in
Hub length	4.72 in
Body width	3.94 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	5820.2 lb
Load capacity at 3.7 mph	4850.16 lb
Electric conductive	no
Stainless	no
Load capacity Static	9700.33 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	33.2 lb




PRODUCT INFORMATION

NOVATECH

FTP 250x100-Ø35 HL120

EAN 4031582319361

Order number 10801911



BETTER MOBILITY. BETTER LIFE.