

PRODUCT INFORMATION

PURETECH AIR

PPR400x100-Ø10 HL129 2ply with axle

EAN 4031582461398



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Puretech air
Type	Wheel
Load capacity at 3 km/h	200 kg
Electric Conductive	No
Stainless	No
Load capacity Static	400 kg
Overall weight	2.04 kg

WHEEL

Tread hardness	soft
Body material	Polypropylene
Tread Material Mix	Pneumatic tyre, line profile
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	400 mm
Tread width	100 mm
Axle Hole Diameter	20 mm
Hub Length	129 mm
Hardness of tread (A)	55 Shore A

PURETECH AIR

PPR400x100-Ø10 HL129 2ply with axle

EAN 4031582461398



BETTER MOBILITY. BETTER LIFE.

Product Drawings

