

STYLEA

5925UOI035L51-9 LOW

EAN 4031582356762



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●●●

otpornost na rdju ●●●●○

OSNOVNI ATRIBUTI

Naziv proizvoda	Stylea
Tip	Okreni Tocak sa kocnica tocka
Standard	EN12528 - tockovi za namestaj
Nosivost na 3 km/h	50 kg
Statički Nosivost	100 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	31 mm
Ukupna širina	52 mm
Ukupna težina	50 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj sa caura cevi
osovina	Zaobilaženje
stitnici omotaca	Bez stražara
Prečnik	35 mm
Širina omotac	11 mm

KUCISTE

Materijal	poliamid
oblik viljuska	kuciste za dva Tocak
okretni lezaj	stablo , okretanje
ofset	12 mm
okretni radijus	45 mm
Otpor okretanju	90 mm
Prečnik kupole	15,2 mm

PRILAGODAVANJE

Tip uklapanja	zatvorena rupa za postavljanje B10
dimenzija rupa sraf	9 mm

STYLEA

5925UOI035L51-9 LOW

EAN 4031582356762



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

