


## NOVATECH

RK.ETP085X90-Ø47X14

EAN 4031582329001  
Broj porudžbine 00828766

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

|                        |           |
|------------------------|-----------|
| Performanse kotrljanja | ● ● ● ● ○ |
| Buka u pokretu         | ● ● ● ○ ○ |
| Ishrana                | ● ● ● ● ○ |
| otpornost na rdju      | ● ● ● ○ ○ |

## OSNOVNI ATRIBUTI

|                                |                              |
|--------------------------------|------------------------------|
| Naziv proizvoda                | Novatech                     |
| Tip                            | Tocak                        |
| Standard                       | EN12532 - transportna oprema |
| Nosivost na 4 km/h             | 800 kg                       |
| Nosivost na 6 km/h             | 640 kg                       |
| Statički Nosivost              | 1600 kg                      |
| Temperaturni opseg (Minimalno) | -10 °C                       |
| Opseg temperature (maksimalni) | 60 °C                        |
| Ukupna težina                  | 1,156 kg                     |

## TOCAK

|                            |                     |
|----------------------------|---------------------|
| Materijal za telo          | Nedefinisani        |
| materijal omotaca          | polipropilen, mekan |
| Prečnik                    | 85 mm               |
| Širina omotac              | 90 mm               |
| Teškoća gazećeg omotac (A) | 92 Šor A            |
| Teškoća gazećeg omotac (D) | 42 Šor D            |
| Prečnik kuglicni lezaj     | 47 mm               |
| Širina kuglicni lezaj      | 14 mm               |

## TEHNIČKI CRTEŽI

