

PRODUCT INFORMATION

# ELASTECH

UFR100x34-Ø20 Grey

EAN 4031582436679



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### WHEEL

Tread hardness	soft
Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.34 in
Axle hole diameter	0.79 in
Hub length	1.75 in
Hardness of tread (A)	64 Shore A

### PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

### CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	352.74 lb
Electric conductive	no
Stainless	no
Load capacity Static	705.48 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	0.54 lb