

# NOVATECH

ETP 082X62-Ø20 HL62

EAN 4031582318685  
Broj porudžbine 00829296

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	82 mm
Širina omotac	62 mm
dimenzija rupa osovina	20 mm
dužina glavčine	62 mm
Širina tela	62 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D
Tip ležaja	6204

## PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	600 kg
Nosivost na 6 km/h	480 kg
Statički Nosivost	1200 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	1,114 kg

# NOVATECH

ETP 082X62-Ø20 HL62

EAN 4031582318685  
Broj porudžbine 00829296



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

