

DURATECH

MOP 100x50-Ø20

EAN 4031582320008



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK


Materijal za telo	poliamid, super težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavcine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6304

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	1680 kg
Nosivost na 6 km/h	1400 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	2800 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0.7 kg




DURATECH

MOP 100x50-Ø20

EAN 4031582320008

Broj porudžbine 00804258



BETTER MOBILITY. BETTER LIFE.