

FOOTMASTER

FOOT MASTER GD- 40-S-NYN

EAN 4031582413199



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product name	Footmaster
Type	Swivel caster
Load capacity at 1.8 mph	132.28 lb
Electric conductive	no
Stainless	no
Load capacity Static	132.28 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	194 °F
Overall height	2.8 in
Overall width	2.28 in
Overall weight	0.71 lb

HOUSING

Housing Color	White
Offset	1.18 in
Swivel radius	2.01 in
Swivel interference	4.02 in
Dome diameter	2.28 in

WHEEL

Bearing	Roller bearing, damped
Wheel color	Black
Diameter	1.65 in
Tread width	0.75 in
Body width	0.75 in

FOOTMASTER

FOOT MASTER GD- 40-S-NYN

EAN 4031582413199

Order number 00062067

Product Drawings



BETTER MOBILITY. BETTER LIFE.

