

PURETECH

PVR125X37-Ø15

EAN 4031582321289
Broj porudžbine 00030754

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ○ ○ ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	100 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,488 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma crna
Nošenje	kotrljajući lezaj
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	37 mm
dimenzija rupa osovina	15 mm
dužina glavcine	58 mm
Teškoća gazećeg omotac (A)	85 Šora A

PURETECH

PVR125X37-Ø15

EAN 4031582321289
Broj porudžbine 00030754



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

