

ALPHA

3470HKP100P30 TZA

EAN 4031582490244



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	128 mm
Overall weight	0.77 kg

WHEEL

Body material	Damping, hybrid material
Tread material	Polypropylene, soft
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	100 mm
Tread width	41 mm
Hardness of tread (A)	98 Shore A

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	38 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	12.5 mm

PRODUCT INFORMATION

ALPHA

3470HKP100P30 TZA

EAN 4031582490244



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

