

ALPHA

3470DIR125R05-20X45

EAN 4031582303438



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	158 mm
Overall weight	1.309 kg

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	125 mm
Tread width	37 mm
Hardness of tread (A)	80 Shore A

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	40 mm
Swivel radius	102.5 mm
Swivel interference	205 mm

FITTING

Fitting type	Solid stem, round
Bolt diameter	20 mm
Bolt length	45 mm

ALPHA

3470DIR125R05-20X45

EAN 4031582303438



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

