

# PURETECH

UVH 080X35 HL46

EAN 4031582323627  
Order number 00002549



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Solid rubber, black
Bearing	Plain bearing
Wheel color	Graphite black (RAL9011)
Threadguards	With threadguard
Diameter	3.15 in
Tread width	1.38 in
Axle hole diameter	0.33 in
Hub length	1.81 in
Body width	1.38 in
Hardness of tread (A)	90 Shore A
Hardness of tread (D)	39 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Puretech
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	0.48 lb

# PURETECH

UVH 080X35 HL46

EAN 4031582323627  
Order number 00002549



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

