

# PURETECH

UVH 080X35 HL46

EAN 4031582323627  
Order number 00002549



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                          |
|-----------------------|--------------------------|
| Body material         | Polyamide                |
| Tread material        | Solid rubber, black      |
| Bearing               | Plain bearing            |
| Wheel color           | Graphite black (RAL9011) |
| Threadguards          | With threadguard         |
| Diameter              | 3.15 in                  |
| Tread width           | 1.38 in                  |
| Axle hole diameter    | 0.33 in                  |
| Hub length            | 1.81 in                  |
| Body width            | 1.38 in                  |
| Hardness of tread (A) | 90 Shore A               |
| Hardness of tread (D) | 39 Shore D               |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Puretech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 220.46 lb                     |
| Load capacity Static        | 440.92 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 176 °F                        |
| Overall weight              | 0.48 lb                       |

# PURETECH

UVH 080X35 HL46

EAN 4031582323627  
Order number 00002549



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

