

MONO

5025PJH080S70-10X15 TFR

EAN 4031582385762



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Mono
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	154.32 lb
Load capacity Static	308.65 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	4.33 in
Overall weight	0.44 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	With threadguard
Diameter	3.15 in
Tread width	0.94 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Polyamide
Fork shape	Closed
Swivel bearing	Stem, swiveling
Offset	1.34 in
Swivel radius	2.91 in
Swivel interference	5.83 in
Thread diameter	0 in

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	0.59 in

PRODUCT INFORMATION

MONO

5025PJH080S70-10X15 TFR

EAN 4031582385762



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

