

# LUMINA

A520POI040P41 TFR

EAN 4031582389746



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Lumina
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	22.05 lb
Load capacity Static	44.09 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	2.13 in
Overall width	1.5 in
Overall weight	0.12 lb

## WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.57 in
Tread width	0.24 in
Hardness of tread (D)	65 Shore D

## HOUSING

Material	Polypropylene
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	Stem, swiveling
Swivel radius	1.42 in
Swivel interference	2.83 in

## FITTING

Fitting type	Square plate
Plate length	1.5 in
Plate width	1.5 in
Plate hole length (Maximum)	1.1 in
Plate hole width (Maximum)	1.1 in