

ALPHA CENTRAL

3476PXU200P69 L0-11

EAN 4031582304992



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha central
Type	Swivel castor with central , total lock
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	451.95 lb
Load capacity Static	903.89 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	9.45 in
Overall weight	5.97 lb

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, biosourced, injected, electric-conductive
Bearing	Plain bearing with synthetic spacer Tube
Axle	Screwed with nut
Diameter	7.87 in
Tread width	1.97 in
Hardness of tread (A)	85 Shore A

HOUSING

Material	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	2.17 in
Swivel radius	6.1 in
Swivel interference	12.2 in

FITTING

Fitting type	Rectangular plate with central locking function
Plate length	5.39 in
Plate width	4.13 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

ALPHA CENTRAL

3476PXU200P69 L0-11

EAN 4031582304992



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

