

STYLEA

5923UAI055L51-10 BIAŁY

EAN 4031582477085



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Type	Swivel castor with intermittennd brake
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	57 mm
Overall width	37 mm
Overall weight	0.65 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	55 mm
Tread width	11 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	47 mm
Swivel interference	94 mm
Dome diameter	18 mm

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm



STYLEA

5923UAI055L51-10 BIAŁY

EAN 4031582477085



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

