

# FOOTMASTER

## FOOT MASTER GAGD-075-ASF-HUD

EAN 4031582496567  
Order number 00800207



Image may differ from the original product

### PERFORMANCE

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○

### CORE ATTRIBUTES

Product name	Footmaster
Type	Swivel castor
Load capacity at 1.8 mph	551.16 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	194 °F
Overall height	4.84 in
Overall width	4.65 in
Overall weight	11.66 lb

### WHEEL

Bearing	Unmachined hub
Diameter	2.95 in
Tread width	1.18 in
Body width	1.18 in

### HOUSING

Offset	1.18 in
Swivel radius	2.83 in
Swivel interference	5.67 in
Dome diameter	4.09 in

### FITTING

Plate length	4.41 in
Plate width	4.41 in
Plate hole length (Maximum)	3.62 in
Plate hole width (Maximum)	3.62 in
Plate hole diameter	0.35 in