

PRODUCT INFORMATION

SUPRATECH

PJR 100x32-Ø12 HL44,4

EAN 4031582320527



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Supratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	80 kg
Electric Conductive	No
Stainless	No
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.17 kg



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Roller bearing
Wheel Color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	100 mm
Tread width	32 mm
Axle Hole Diameter	12 mm
Hub Length	44.4 mm
Body width	32 mm
Hardness of tread (A)	87 Shore A

SUPRATECH

PJR 100x32-Ø12 HL44,4

EAN 4031582320527

Order number 00030822
Product Drawings



BETTER MOBILITY. BETTER LIFE.

