

# ALPHA STAINLESS

8470UFX125P30-11

EAN 4031582370126



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Alpha stainless               |
| Type                        | Swivel caster                 |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 330.69 lb                     |
| Electric conductive         | no                            |
| Stainless                   | Yes                           |
| Load capacity Static        | 661.39 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 176 °F                        |
| Overall height              | 6.1 in                        |
| Overall weight              | 2.38 lb                       |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Housing Material    | Stainless steel, heavy |
| Fork shape          | Broad                  |
| Swivel bearing      | Two ball races         |
| Housing Color       | Stainless steel        |
| Offset              | 1.57 in                |
| Swivel radius       | 4.04 in                |
| Swivel interference | 8.07 in                |

## WHEEL

|                       |                                       |
|-----------------------|---------------------------------------|
| Tread hardness        | soft                                  |
| Body material         | Polyamide                             |
| Tread material        | Elastic tire, non-marking, vulcanized |
| Bearing               | Precision ball bearing, sealed        |
| Axle                  | Screwed with nut                      |
| Threadguards          | With threadguard                      |
| Diameter              | 4.92 in                               |
| Tread width           | 1.57 in                               |
| Hardness of tread (A) | 64 Shore A                            |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 0.43 in   |

# ALPHA STAINLESS

8470UFX125P30-11

EAN 4031582370126

Order number 00038473  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

