

## BINNENBAND 260X85

EAN 4031582328066



Image may differ from the original product

### PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

### CORE ATTRIBUTES

Product name	Accessory
Housing type	Accessory
Load capacity at 1.8 mph	330.69 lb
Load capacity Static	661.39 lb

### WHEEL

Diameter	10.24 in
Tread width	3.35 in
Suitable for	dpr