

# PLATE

P11-40X27 / 8

EAN 4031582320213



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Corrosion resistance ● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Plate
Type	Accessory
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Overall height	8 mm

## FITTING

Fitting type	Stem with L-shaped plate
Plate length	40 mm
Plate width	27 mm
Plate hole length (Maximum)	32 mm
Plate hole width (Maximum)	32 mm
Plate hole diameter	4 mm