

ALPHA

8499UFX160P67 Q1-11

EAN 4031582380774



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Movement noise ○ ○ ○ ○ ○

CORE ATTRIBUTES

Product name	Alpha
Type	Fixed castor
Load capacity at 1.8 mph	661.39 lb
Load capacity at 2.5 mph	661.39 lb
Load capacity at 3.7 mph	440.92 lb
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall height	7.87 in
Overall weight	4.39 lb

WHEEL

	soft
Bearing	Precision ball bearing, sealed
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	6.3 in
Tread width	1.81 in
Hardness of tread (A)	64 Shore A

HOUSING

Material	Stainless steel, heavy
Fork shape	Broad

FITTING

Plate length	5.39 in
Plate width	4.53 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in

ALPHA

8499UFX160P67 Q1-11

EAN 4031582380774



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

