

# ELASTECH

UEP160x40-Ø20 TFR

EAN 4031582394481



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Elastech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 250 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 500 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 80 °C                         |
| Overall weight              | 0.81 kg                       |

## WHEEL

|                       |                                 |
|-----------------------|---------------------------------|
| Tread hardness        | soft                            |
| Body material         | Polyamide                       |
| Tread Material Mix    | Elastic tire, black, vulcanized |
| Bearing               | Precision ball bearing          |
| Threadguards          | With threadguard                |
| Diameter              | 160 mm                          |
| Tread width           | 40 mm                           |
| Axle Hole Diameter    | 20 mm                           |
| Hub Length            | 60 mm                           |
| Hardness of tread (A) | 64 Shore A                      |

