PRODUCT INFORMATION

ELASTECH

UEP160x40-Ø20 TFR

EAN 4031582394481



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Polyamide
Tread Material Mix	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	160 mm
Tread width	40 mm
Axle Hole Diameter	20 mm
Hub Length	60 mm
Hardness of tread (A)	64 Shore A

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●●●
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Electric Conductive	No
Stainless	No
Load capacity Static	500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.81 kg

© Copyright 2026 TENTE International GmbH


ELASTECH

UEP160x40-Ø20 TFR

EAN 4031582394481

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH