

# SCOUT

814WQSC200P60 180°

Order number 00865844



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Scout
Housing type	Swivel castor with spring loaded directional lock and wheel brake
Standard	similar EN12532 - Transport Equipment
Load capacity at 4 km/h	350 kg
Electric conductive	✓
Load capacity Static	700 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall height	245 mm
Overall width	74 mm
Overall weight	3.359 kg

## WHEEL

Body material	Polyurethane injected
Tread material	Polyurethane, injected, electric-conductive
Bearing	Precision ball bearing, stainless
Threadguards	With threadguard
Diameter	200 mm
Tread width	40 mm
Hardness of tread (A)	85 Shore A

## HOUSING

Material fork	Stainless steel, heavy
Fork shape	Angular
Swivel bearing	Precision ball bearing
Offset	50 mm
Swivel radius	162.5 mm
Swivel interference	325 mm
Dome diameter	68 mm
Stainless	✓

## FITTING

Fitting type	Rectangular plate
Plate length	130 mm
Plate width	74 mm
Plate hole length (Maximum)	110 mm
Plate hole width (Maximum)	50 mm
Plate hole diameter	10.5 mm

# SCOUT

814WQSC200P60 180°

Order number 00865844



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

