

# MAXTECH

PNP 200x30-Ø8 HL44

EAN 4031582320626



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Tread hardness        | soft                   |
| Body material         | Polypropylene          |
| Tread material        | Polyurethane, foamed   |
| Bearing               | Precision ball bearing |
| Wheel color           | Black                  |
| Threadguards          | With threadguard       |
| Diameter              | 7.87 in                |
| Tread width           | 1.18 in                |
| Axle hole diameter    | 0.31 in                |
| Hub length            | 1.73 in                |
| Body width            | 1.18 in                |
| Hardness of tread (A) | 70 Shore A             |

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○   |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Maxtech                       |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 220.46 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 440.92 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall weight              | 0.88 lb                       |

# MAXTECH

PNP 200x30-Ø8 HL44

EAN 4031582320626

Order number 00005568  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

