PRODUCT INFORMATION

# MAXTECH

## PNP 200x30-Ø8 HL44

EAN 4031582320626




Image may differ from the original product

### WHEEL

| | |
|---|---|
| Tread hardness | soft |
| Body material | Polypropylene |
| Tread material | Polyurethane, foamed |
| Bearing | Precision ball bearing |
| Wheel color | Black |
| Threadguards | With threadguard |
| Diameter | 7.87 in |
| Tread width | 1.18 in |
| Axle hole diameter | 0.31 in |
| Hub length | 1.73 in |
| Body width | 1.18 in |
| Hardness of tread (A) | 70 Shore A |

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●●○ |
| Attrition | ●●●○○ |
| Corrosion resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product name | Maxtech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 220.46 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 440.92 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall weight | 0.88 lb |

© Copyright 2026 TENTE International GmbH


# MAXTECH

## PNP 200x30-Ø8 HL44

EAN 4031582320626

Order number 00005568

**Product Drawings**




© Copyright 2026 TENTE International GmbH