

# KAPPA LOAD

9652TOP200P63 CL67

EAN 4031582314946  
Order number 00828520



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ○ ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                                   |
|-----------------------------|---------------------------------------------------|
| Product name                | Kappa load                                        |
| Type                        | Swivel castor with total lock, head end of castor |
| Standard                    | EN12533 - Heavy Duty Castors                      |
| Load capacity at 4 km/h     | 1200 kg                                           |
| Load capacity at 6 km/h     | 1000 kg                                           |
| Load capacity Static        | 2000 kg                                           |
| Temperature range (Minimum) | -30 °C                                            |
| Temperature range (Maximum) | 80 °C                                             |
| Overall height              | 245 mm                                            |
| Overall width               | 116 mm                                            |
| Overall weight              | 5.309 kg                                          |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polyamide, heavy          |
| Tread material        | Identical with wheel body |
| Bearing               | Precision ball bearing    |
| Axle                  | Screwed with nut          |
| Wheel color           | Natural white             |
| Threadguards          | Without threadguard       |
| Diameter              | 200 mm                    |
| Tread width           | 50 mm                     |
| Body width            | 50 mm                     |
| Hardness of tread (D) | 75 Shore D                |

## HOUSING

|                     |                                        |
|---------------------|----------------------------------------|
| Material fork       | Iron forged, heavy                     |
| Fork shape          | Broad, reinforced                      |
| Swivel bearing      | Deep-groove ball thrust roller bearing |
| Colour              | Blue passivated                        |
| Offset              | 59 mm                                  |
| Swivel radius       | 160 mm                                 |
| Swivel interference | 320 mm                                 |
| Lubrication nipple  | ✓                                      |
| Dome diameter       | 111 mm                                 |

## FITTING

|                             |                          |
|-----------------------------|--------------------------|
| Fitting type                | Medium rectangular plate |
| Plate length                | 135 mm                   |
| Plate width                 | 110 mm                   |
| Plate hole length (Minimum) | 75 mm                    |
| Plate hole length (Maximum) | 80 mm                    |
| Plate hole width (Minimum)  | 75 mm                    |
| Plate hole width (Maximum)  | 105 mm                   |
| Plate hole diameter         | 11 mm                    |

# KAPPA LOAD

9652TOP200P63 CL67

EAN 4031582314946  
Order number 00828520



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

