

COMPACTA

2198UOI045P60-67X24,5-TFR

EAN 4031582477542



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Compacta
Type	Fixed castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	48.5 mm
Overall weight	0.063 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	45 mm
Tread width	18 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Angular

FITTING

Fitting type	Rectangular plate
Plate length	67 mm
Plate width	24.5 mm
Plate hole length (Maximum)	54 mm
Plate hole width (Maximum)	54 mm
Plate hole diameter	5.2 mm

COMPACTA

2198UOI045P60-67X24,5-TFR

EAN 4031582477542



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

